

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0190560065**
Status: **Active**
Overview: VersaKrimp Terminals and Splices
Description: VersaKrimp Ring Tongue Terminal for 14-16 AWG Wire, Non-Insulated, Stud Size 6

Documents:

Drawing (PDF)	Product Specification PS-19902-011-001 (PDF)
Product Specification 194130109-000 (PDF)	Product Specification PS-19902-013-001 (PDF)
Product Specification 194130110-000 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Ring and Spade Terminals
Series	<u>19056</u>
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Overview	<u>VersaKrimp Terminals and Splices</u>
Product Name	VersaKrimp
Type	Ring
UPC	800755063370

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.708/g
Packaging Type	Carton
Stud Size	6 (M3.5)
Temperature Range - Operating	149°C
Termination Interface: Style	Crimp or Compression
Wire Size AWG	14, 16
Wire Size mm ²	1.00-2.50

Solder Process Data


Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Engineering Number	B-323-06
--------------------	----------

Reference - Drawing Numbers

Product Specification	194130109-000, 194130110-000, PS-19902-011-001, PS-19902-013-001
Sales Drawing	BCD30101



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

19056 Series

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

PremiumGrade Hand	<u>640030100</u>
Crimp Tool	
Crimp Head for the	<u>640070100</u>
AT-200 Pneumatic	
Hand Tool	