

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0700580069](#)
Status: **Active**
Overview: C-Grid Connector Products
Description: SL Crimp Terminal, Female, 24-30 AWG, with Tin (Sn) Plated Contact, Unplated Edges, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
 Series [70058](#)
 Application Signal, Wire-to-Board, Wire-to-Wire
 Crimp Quality Equipment Yes
 Overview [C-Grid Connector Products](#)
 Packaging Alternative [700580096 \(Bag\)](#)
 Product Name CyClone, SL
 UPC 822350748179

Physical

Gender Female
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Net Weight 0.075/g
 Packaging Type Reel
 Plating min - Mating 3.810µm
 Plating min - Termination 3.810µm
 Termination Interface: Style Crimp or Compression
 Wire Insulation Diameter 1.52mm max.
 Wire Size AWG 24, 26, 28, 30
 Wire Size mm² N/A


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Sales Drawing 700580000-SD-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
 -ED/88/2018 (15
 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[70058](#) Series

Use With

SL Crimp Housing [70066](#) , [70450](#)

CyClone Connector [73099](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description

Product #

Insertion Tool [11020022](#)

Extraction Tool [11030036](#)

Hand Crimp Tool For [638258800](#)

SL Crimp Terminals

FineAdjust Applicator [639001500](#)

for SL Female Crimp
 Terminal, Insulation

OD 0.63-1.00mm,
 24-30 AWG Wire

FineAdjust Applicator 639003100
for SL Female Crimp
Terminal, Insulation
OD 1.01-1.52mm,
24-30 AWG Wire
T2 Terminator 639103100
Tooling Die

This document was generated on 04/01/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION