

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0330015005](#)

Status: **Active**

Overview: [MX150 Sealed and Unsealed Connector System](#)

Description: MX150 Female Terminal Sealed, Silver Plating, Grip Code M3, Preferred Terminal for use in Sealed Application with 0.35-0.50mm², Left Reel Payoff

Documents:

Drawing (PDF)	Application Specification AS-33012-002-CH-001 (PDF)
Product Specification PS-33012-002-001 (PDF)	Application Specification AS-33012-002-FR-001 (PDF)
Product Specification TS-33001-003-001 (PDF)	Packaging Specification 313025040-000 (PDF)
Product Specification TS-33001-004-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33012-002-001 (PDF)	

General

Product Family	Crimp Terminals
Series	33001
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	Left Reel Payoff, Small Polarization Rib, Left Reel Payoff, Small Polarization Rib
Crimp Quality Equipment Overview	Yes
Product Name	MX150 Sealed and Unsealed Connector System
UPC	MX150 884982250864

Physical

Gender	Female
Grip Code	M3
Material - Metal	High Performance Alloy (HPA)
Material - Plating Mating	Silver
Material - Plating Termination	Tin
Net Weight	0.443/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.70mm max.
Wire Size AWG	N/A
Wire Size mm ²	0.35-0.50

Electrical

Current - Maximum per Contact	Contact Molex
Voltage - Maximum	14V DC

Material Info

Reference - Drawing Numbers

Application Specification	AS-33012-002-001, AS-33012-002-CH-001, AS-33012-002-FR-001
Packaging Specification	313025040-000
Product Specification	PS-33012-002-001, TS-33001-003-001, TS-33001-004-001
Sales Drawing	SD-33012-002



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -ED/88/2018 (15 January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[33001](#) Series

Use With

[33472](#) Dual Row Housing. [33476](#) Hybrid Housing. [33471](#) Single Row Housing

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FA2 Mechanical Feed Applicator for MX150 Female Terminals, 0.35mm ² and 0.50mm ² ISO Wire	638082500
Manual Extraction Tool	638131500

Hand Crimp Tool for [638233700](#)
ISO (M3) Receptacle
Terminals
FineAdjust Applicator [639041200](#)
for SRC Connector
using MX150
Receptacle
Terminals, 0.50mm²
wires

This document was generated on 04/17/2019

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION