

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0934453201](#)  
**Status:** **Active**  
**Overview:** [ML-XT Sealed Connection System](#)  
**Description:** ML-XT Sealed 4 Circuit Plug Housing, Pre-Assembled with Large Rear Seal and Cover, Black

**Documents:**

|   |   |
|---|---|
| <a href="#">3D Model</a>                                    | <a href="#">Packaging Specification 934430002-K (PDF)</a> |
| <a href="#">Drawing (PDF)</a>                               | <a href="#">RoHS Certificate of Compliance (PDF)</a>      |
| <a href="#">Product Specification 934430010-P (PDF)</a>     | <a href="#">Product Literature (PDF)</a>                  |
| <a href="#">Application Specification 934430010-A (PDF)</a> |   |



**Agency Certification**

UL E29179

**Application tooling part link**

Application Tooling Part Link 63824-5300

**General**

|                             |  |
|-----------------------------|--|
| Product Family              | Crimp Housings                                 |
| Series                      | <a href="#">93445</a>                          |
| Application                 | Power, Signal, Wire-to-Wire                    |
| Overview                    | <a href="#">ML-XT Sealed Connection System</a> |
| Product Literature Order No | 987651-0201                                    |
| Product Name                | ML-XT  |
| UPC                         | 889056164566                                   |

**Physical**

|                               |                |
|-------------------------------|----------------|
| Circuits (maximum)            | 4              |
| Color - Resin                 | Black          |
| Gender                        | Plug           |
| Glow-Wire Capable             | No             |
| Keying to Mating Part         | None           |
| Lock to Mating Part           | Yes            |
| Material - Resin              | Nylon          |
| Net Weight                    | 6.634/g        |
| Number of Rows                | 2              |
| Packaging Type                | Bag            |
| Panel Mount                   | No             |
| Pitch - Mating Interface      | N/A            |
| Polarized to Mating Part      | Yes            |
| Temperature Range - Operating | -55° to +125°C |

**Electrical**

Current - Maximum per Contact 13.0A

**Material Info**

**Reference - Drawing Numbers**

|                           |               |
|---------------------------|---------------|
| Application Specification | 934430010-A   |
| Packaging Specification   | 934430002-K   |
| Product Specification     | 934430010-P   |
| Sales Drawing             | 934430030-000 |

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/01/2018 (15  
January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93445 Series](#)

**Mates With**

ML-XT Sealed 4 Circuit Receptacle Housing  
[934443201](#)

**Use With**

ML-XT Female (Socket) Terminal  
[845250009](#) (Nickel), ML-XT Female (Socket)  
Terminal [845250032](#) (Selective Gold), ML-  
XT 4 Circuit Plug Wedgelock [93448](#) , ML-XT  
Blind Cavity Plug [934941000](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

|                                     |                           |
|-------------------------------------|---------------------------|
| Extraction Tool<br>for ML-XT Sealed | <a href="#">638245300</a> |
|-------------------------------------|---------------------------|

This document was generated on 04/05/2019

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**