

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0845250032](#)
Status: **Active**
Overview: [ML-XT Sealed Connection System](#)
Description: ML-XT / XRC Female (Socket) Terminal, 16 to 18 AWG, Terminal Size 16, Insulation Diameter 1.40 to 2.16mm, Selective Gold

Documents:

Drawing (PDF)	Packaging Specification 845250001-K (PDF)
Product Specification PS-84501-001-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification 845241000-A (PDF)	Product Literature (PDF)

General

Product Family	Crimp Terminals
Series	84525
Application	Power
Crimp Quality Equipment	Yes
Overview	ML-XT Sealed Connection System
Product Literature Order No	987651-0201
Product Name	ML-XT, XRC
UPC	78172511503


Physical

Gender	Female
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Net Weight	0.420/g
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.40-2.16mm
Wire Size AWG	16, 18
Wire Size mm ²	0.82-1.31

Material Info

Reference - Drawing Numbers

Application Specification	845241000-A
Packaging Specification	845250001-K
Product Specification	PS-84501-001-001
Sales Drawing	845250010-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/88/2018 (15
January 2019)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[84525 Series](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool for 3.56mm Crimp Terminal, Pin FineAdjust	638115500
Applicator, Insulation Range 1.40–1.79mm FineAdjust	638681000
Applicator, Insulation Range 1.79-2.16mm	638681100