



devolo

devolo Magic 1 WiFi 211

Technical data

Standards	IEEE 802.3, IEEE 802.3u, IEEE 802.3x, IEEE 802.11 a, b, g, n, ac (2.4 / 5 GHz concurrent) , IEEE 1905.1, IEEE 802.3az, IEEE 802.1p Auto MDI/X HomeGrid Forum (HGF)
Transmission speeds	Wi-Fi 867 (mbps, 2x2 MIMO/ 5 GHz), Wi-Fi 300 (mbps, 2x2 MIMO/ 2,4 GHz) Ethernet 10/100 (mbps) Powerline 1200 (mbps)
Modulation • Carrier	Powerline OFDM - 4096/1024/256/64-QAM, QPSK, BPSK Wi-Fi DSSS (IEEE 802.11b) • Wi-Fi OFDM (IEEE 802.11a, g, n, ac) • WiFi 32
Range (in m)	Powerline: 400 Wi-Fi: 300
Security	WPA/WPA2 WPS PIN, WPS PBC MAC-Address Filter Wi-Fi Time Schedule 128 Bit AES
LEDs	PLC (multi) WiFi
Buttons	Pairing Wi-Fi on/off WPS Factory Default
Socket • Connector • Countries	Type G (BS 1363) • Type G (BS 1363) • (UK) Type G (UK only) Body up • (none) • (UKBO)
Power output to integrated socket	13 A
Device port	2 x Ethernet RJ45 4 x Antenna
Power consumption	Maximum W/A: 7,6 W Typical W/A: 5,1 W Stand-By W/A: 2,0 W
Power supply	internal 196-250 V AC 50 Hz
Attenuation filter	2 - 80 MHz
Filter characteristics	-22 db to -45 db
Temperature (Storage • Operating)	-25°C to 70°C • 0°C to 40°C



devolo

Dimensions (in mm, without plug)	152 x 76 x 40 (the same as LAN 1200+ Wi-Fi ac)
Ambient conditions	10-90% Humidity (non-condensing)
Operating systems	Windows 7 (32 Bit), Windows 7 (64 Bit) Windows 8.x (32 Bit), Windows 8.x (64 Bit), Windows 8.x Pro (32 Bit), Windows 8.x Pro (64 Bit), Windows 10.x Pro (32 Bit), Windows 10.x Pro (64 Bit) MAC OS X 10.10, MAC OS X 10.11, MAC OS X 10.12 Windows, MAC OS X, Ubuntu-Linux
Certifications	CE Class B (EU, CH, NO)
Additional features	Interfaces can be enabled/disabled, HTML configuration page

Sales information

Warranty (in years)	3
Accessories	Printed Install Flyer Ethernet Cable(s)

Single adapter

8353 (UK)

EAN: 4250059683532
Weight: 570 g
Dimensions: 190 x 118 x 92 mm

WEEE additional information:

Weight WEEE: 360 g
Paper (Green Dot): 175 g
Plastic (Green Dot): 2 g
other (Green Dot): 0 g

Starter Kit

8361 (UK)

EAN: 4250059683617
Weight: 890 g
Dimensions: 188 x 231 x 92 mm

WEEE additional information:

Weight WEEE: 625 g
Paper (Green Dot): 225 g
Plastic (Green Dot): 4 g
other (Green Dot): 0.2 g

Network Kit

8369 (UK)

EAN: 4250059683693
Weight: 1265 g
Dimensions: 188 x 231 x 92 mm

WEEE additional information:

Weight WEEE: 985 g
Paper (Green Dot): 240 g
Plastic (Green Dot): 6 g
other (Green Dot): 0.2 g

© 2018 devolo AG, Germany. All rights reserved.
Technical data subject to change without notice.

Version: en_UK 09.08.2018

devolo AG . Charlottenburger Allee 67 . 52068 Aachen . Tel.: +49 (0) 241 182 79 0 . Fax.: +49 (0) 241 182 79 99 . www.devolo.com . info@devolo.com
Sales contact:

devolo UK Limited . The Oxford Science Park . Robert Robinson Avenue 1 . OX4 4GA Oxford . Phone: +44 1865 784344 . www.devolo.co.uk . info@devolo.co.uk