

Description

Brand new for 2019 Game Max are proud to introduce the Strike RGB Gaming Mouse, the first RGB mouse to be introduced into the Game Max family. The Strike is a 6D optical gaming mouse, finished with a rubber coating, fantastic lighting that runs all around the bottom of the mouse and adjustable sensitivity.

The Strike comes with an RGB backlight that has several different LED modes, easily changed using a button on the bottom of the mouse. It is the right balance between a strong, quality RGB light and modern design that it will easily fit in to any set-up.

The Strike also comes with 4 preset DPI settings: "1200/1600/2400/3200", letting you programme the sensitivity.

The ergonomic shape of the mouse gives gamers precise positioning and the most comfortable gaming experience. In line with the Game Max ethos this case offers style, performance and the ultimate experience.



Key Features

- **Design** - The Game Max Strike is ergonomic designed to fit perfectly into your hand and the individually sculpted buttons are carefully designed and placed to be easily identifiable by your touch.
- **RGB Backlighting** - The Strike comes with multiple RGB colour options that light the edge of the mouse and the Game Max logo comes with 4 different colour options at the touch of button allows you to personalise your mouse the way you want.
- **On-The-Fly Adjustable DPI** - Ideal for first time and experienced gamers with a 3200dpi optical sensor you can now get the right level of precision and pixel precise targeting.
- **USB Connection** - The Strike comes with a USB connector, plug and play and with a 1000 millisecond report rate, the Strike communicates as fast as USB can go.
- **Braided Cable** - The USB connector comes with braided cable offering excellent durability and will last a lot longer than a standard cable.

Specifications

Connectivity : USB
Button Qty: 7 Buttons (Included LED Button)
LED Colour: RGB (Game Max Logo: Red, Blue, Pink & Purple)
Materials: ABS
Cable Length : 1.8m
Resolution: 1200 / 1600 / 2000 / 3200 DPI
Button M.T.B.F.: 3 million keystrokes
Maximum Acceleration: 8G
Mouse Type: Optical
Mouse Grip: 4000fps
On-Sensor Code: A704C
Maximum Tracking Speed: 30 Inch/Second
Polling Rate: 125HZ
Working Power: 5V = 100mA
Working Voltage: 5V

Working Current: 100mA (max.)

Current:

Software Compatibility : Windows 2000 / XP / ME / Vista / 7 / 8 / 10 / Linux /

Mac OSX / Android

Net Weight: 140g ± 10g

General Specifications

Manufacturer Part Number: GMX-MS-STRIKE

EAN Number: 5055492407887

Has Mains Plug: No

Colour: Black

What's In The Box: Mouse

User Manual

Unit (Product)

Dimensions (mm): 59mm x 41mm x 124mm (W x H x D)

Packaging

Dimensions (mm): 150mm x 203mm x 52mm (W x H x D)

Net Weight (KGs): 0.13 KGs

Gross Weight (KGs): 0.2 KGs