

# TAB4 8 ZA2B0074GB

## Product

Lenovo TB-8504F

## Region

UKI

## Country

United Kingdom

## Machine Type

ZA2B

## Processor

Qualcomm APQ8017 (4C, 4x A53 @ 1.4GHz)

## Graphics

Integrated Qualcomm Adreno 308 GPU

## Display

8" HD (1280x800) IPS

## Multi-touch

10-point Multi-touch

## Memory

2GB Soldered

## Storage

16GB eMMC

## WLAN + Bluetooth

11b/g/n, 1x1 + BT4.0

## WWAN

None

## Color

Slate Black

## Camera

Front 2.0MP / Rear 5.0MP

## Microphone

Monaural

## Fingerprint Reader

None

## VoiceCall

No

## Battery

1-cell (4850mAh)

## Power Adapter

5V/1.0A

## Bundled Software

None

## Bundled Accessories

None

## Operating System

Android 7.1

## Warranty

1-year

## EAN / UPC

192076997312

## Ann Date (mm/yy)

04/19

### Notes:

Battery life is an estimated maximum. Actual battery life may vary based on many factors, including screen brightness, active applications, features, power management settings, battery age and conditioning, and other customer preferences. <https://www.lenovo.com/hk/en/battery-info>



[WWW.LENOVO.COM](http://WWW.LENOVO.COM)

This publication was developed for products and services offered in the United States and E.M.E.A countries. Lenovo may not offer the products, services or features discussed in this document in other countries. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication “as is” without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.



<https://psref.lenovo.com>

Visit psref website for the latest version of Product Specifications Reference. © Lenovo, 2019. All rights reserved.



# Lenovo TAB4 8 Platform Specifications

Product Specifications Reference (PSREF)

Processor	Qualcomm® Snapdragon™ Processor <b>MSM8917</b> for LTE models 64-bit Quad-Core Processor (ARM Cortex-A53, up to 1.4GHz) <b>APQ8017</b> for WiFi models 64-bit Quad-Core Processor (ARM Cortex-A53, up to 1.4GHz)	Dimensions Weight Case color Case material	<i>HxWxT:</i> 8.31" x 4.88" x 0.33"; 211mm x 124mm x 8.3mm 0.7lb / 320g Slate black or polar white Plastic			
Graphics	Qualcomm Adreno™ 308 in processor	Ports	One Micro USB 2.0 for power charge and data sync, audio combo jack, one MicroSD card slot (WiFi model) or Dual SIM card slot (LTE model) <i>* Depending on many factors, actual data transfer speed may be lower than theoretical speed</i>			
Memory	2GB / LPDDR3, soldered to systemboard	Camera	<i>Front camera:</i> 2.0-megapixel, fixed focus <i>Rear camera:</i> 5.0-megapixel, auto focus			
Display	8.0" (203mm) HD (800x1280), color depth 8-bit, color gamut 60%, 350 nits, 16:10 aspect ratio, IPS display	Audio support	2 x front -facing speakers / single microphone, Dolby Atmos® audio, 3.5mm combo audio / microphone jack			
Multi-touch	Multi-touch, support 10 fingers	Keyboard Touchpad	None None			
Storage	16GB eMMC (embedded Multi Media Card) flash memory on board	Security chip Fingerprint reader	None None			
Card slot	<i>WiFi model :</i> MicroSD card slot, support FAT32 up to 128GB <i>LTE model :</i> Dual Nano-SIM slot, support dual Nano-SIM cards or Nano-SIM card + MicroSD card (up to 128GB)	Bundled software VoiceCall (opt)	Master Data Management (MDM), only available on selected model Support voice call, only on selected LTE models			
Optical	None	Battery type Battery life	Li-ion Polymer 1-cell (4850mAh) General Usage : Up to 20 hr Standby Time : Over 2 weeks Video (720p) playback Time : Over 10 hr Browsing Time: • WiFi : Over 10 hr • LTE : Over 10 hr <i>* Battery life varies significantly with settings, usage, &amp; other factors</i>			
Ethernet	None	AC adapter Preload	5V/1A AC adapter Android® Nougat 7.1 • Lenovo SYNCit • Lenovo SHAREit • Lenovo Framework • Lenovo User Experience (UE) • Google Calendar • Netflix® • Skype™			
Bluetooth®	Bluetooth 4.0 wireless, disabled on some models	Limited warranty	1-year or 2-year limited warranty			
WLAN	802.11 b/g/n, 1x1, single channel (2.4 GHz)	Environment	RoHS-compliant			
WWAN (optional)	4G LTE connectivity					
LTE Band	<table border="1"> <thead> <tr> <th>PRC</th> <th>ROW</th> </tr> </thead> <tbody> <tr> <td>GSM: B2/3/5/8 UMTS: B1/2/5/8 CDMA/EVDO: BC0 TD-SCDMA: B34/39 FDD-LTE: B1/3 TDD-LTE: B38/39/40/41 (narrow band)</td> <td>GSM: B2/3/5/8 UMTS: B1/2/5/8 FDD-LTE: B1/3/5/7/8/20 TDD-LTE: B38/40</td> </tr> </tbody> </table>	PRC	ROW	GSM: B2/3/5/8 UMTS: B1/2/5/8 CDMA/EVDO: BC0 TD-SCDMA: B34/39 FDD-LTE: B1/3 TDD-LTE: B38/39/40/41 (narrow band)	GSM: B2/3/5/8 UMTS: B1/2/5/8 FDD-LTE: B1/3/5/7/8/20 TDD-LTE: B38/40	
PRC	ROW					
GSM: B2/3/5/8 UMTS: B1/2/5/8 CDMA/EVDO: BC0 TD-SCDMA: B34/39 FDD-LTE: B1/3 TDD-LTE: B38/39/40/41 (narrow band)	GSM: B2/3/5/8 UMTS: B1/2/5/8 FDD-LTE: B1/3/5/7/8/20 TDD-LTE: B38/40					
NFC	None					
Vibrator	Vibrator					
G-sensor	G-sensor					
P-sensor	P-sensor (LTE model only)					
L-sensor	L-sensor (LTE model only)					
GPS	ROW: GPS+GLONASS; PRC: GPS+Beidou					
A-GPS	A-GPS (LTE model only)					
E-compass	None					
Hall Sensor	None					
Gyroscope	None					
Proofing	None					

Note: The specifications above may not be available in all regions

Lenovo  
March 2019



TAB4 8

