

### Connection Products

#### Copper Tube Terminals and Copper Tube Butt Splices

Suitable for the termination of cables and stud connectors and splices for joining cable together.


#### Features and Benefits

- Material: High conductivity copper BS EN12449
- Purity: >99.9%
- Coating: Electro Tin Plating to BS1872
- Terminals have flared (bell mouth) entry for ease of cable insertion
- Terminals have inspection holes to check that the cable is inserted properly before terminal is crimped to the cable
- Range covers cable sizes from 6mm to 300mm
- Packed in polythene (PE) bags with Euro slot



*Copper Tube Terminals.*

TYPE	To fit cable size mm	Stud Dia mm	Pack Cont.
HCT 6-4	6.0	4.0	100
HCT 6-6	6.0	6.0	100
HCT 6-8	6.0	8.0	100
HCT 6-10	6.0	10.0	100
HCT 10-6	10.0	6.0	100
HCT 10-8	10.0	8.0	100
HCT 10-10	10.0	10.0	100
HCT 10-12	10.0	12.0	100
HCT 16-6	16.0	6.0	100
HCT 16-8	16.0	8.0	100
HCT 16-10	16.0	10.0	100
HCT 16-12	16.0	12.0	100
HCT 25-6	25.0	6.0	100
HCT 25-8	25.0	8.0	100
HCT 25-10	25.0	10.0	100
HCT 25-12	25.0	12.0	100
HCT 35-6	35.0	6.0	100
HCT 35-8	35.0	8.0	100
HCT 35-10	35.0	10.0	100
HCT 35-12	35.0	12.0	100
HCT50-6	50.0	6.0	50
HCT 50-8	50.0	8.0	50
HCT 50-10	50.0	10.0	50
HCT 50-12	50.0	12.0	50
HCT 70-6	70.0	6.0	50
HCT 70-8	70.0	8.0	50
HCT 70-10	70.0	10.0	50




## Connection Products

### HCT Series

TYPE	To fit cable size mm	Stud Dia mm	Pack Cont.
HCT 70-12	70.0	12.0	50
HCT 70-14	70.0	14.0	50
HCT 70-16	70.0	16.0	50
HCT 95-8	95.0	8.0	5
HCT 95-10	95.0	10.0	5
HCT 95-12	95.0	12.0	5
HCT 95-14	95.0	14.0	5
HCT 95-16	95.0	16.0	5
HCT120-8	120.0	8.0	5
HCT 120-10	120.0	10.0	5
HCT 120-12	120.0	12.0	5
HCT120-14	120.0	14.0	5
HCT 120-16	120.0	16.0	5
HCT 150-10	150.0	10.0	5
HCT 150-12	150.0	12.0	5
HCT150-14	150.0	14.0	5
HCT150-16	150.0	16.0	5
HCT 185-10	185.0	10.0	5
HCT 185-12	185.0	12.0	5
HCT 185-14	185.0	14.0	5
HCT 185-16	185.0	16.0	5
HCT240-10	240.0	10.0	5
HCT240-12	240.0	12.0	5
HCT 300-10	300.0	10.0	5
HCT 300-12	300.0	12.0	5
HCT 300-16	300.0	16.0	5





## Copper Tube Terminals and Copper Tube Butt Splices

HCBS Series



*Copper Tube Butt Splices.*

TYPE	Description	Cable Cross Section mm	Pack Cont.
HCBS6	Copper Tube Butt Splice	6.0	50
HCBS10	Copper Tube Butt Splice	10.0	25
HCBS16	Copper Tube Butt Splice	16.0	25
HCBS25	Copper Tube Butt Splice	25.0	25
HCBS35	Copper Tube Butt Splice	35.0	25
HCBS50	Copper Tube Butt Splice	50.0	10
HCBS70	Copper Tube Butt Splice	70.0	10
HCBS95	Copper Tube Butt Splice	95.0	10
HCBS120	Copper Tube Butt Splice	120.0	5
HCBS150	Copper Tube Butt Splice	150.0	5
HCBS185	Copper Tube Butt Splice	18.0	5
HCBS240	Copper Tube Butt Splice	240.0	5
HCBS300	Copper Tube Butt Splice	300.0	5



Full range of tooling available see page  
65-67