

# Special WX Soldering Station and Precision Tool Bundle

## Weller WX 2-Channel Soldering Station



### WX2021N 2-Channel Soldering Station

- + Compatible with WXMT-MS desoldering tweezers
- + Compatible with all WX series soldering pencils
- + Multi-purpose USB port for parameter configuration and data logging
- + Acts as a benchtop controller for the Zero Smog 4V / 6V Filtration units
- + Acts as a benchtop controller for the WHP1000 / WHP3000 hot plates
- + Multi-language menu navigation
- + Turn-and-click wheel with enter key and finger guide is intuitive to use
- + Capacitive glass touch screen is chemical and temperature resistant
- + Large graphic LCD display can be viewed from all angles

### Weller Erem® 632N Side Cutter – Oval Head

- + Fits for all cutting applications where easy access is given
- + Robust and size-for-size offers the highest cutting capacity
- + The most widely used head shape

List Price: \$1,150

Exclusive Promo Price: \$999



**Weller®**

## Weller High Powered Digital Soldering Station, 200W, 120 V W/WXMP & WXMT

◀◀ previous print close next ▶▶



### Product Details

<b>Catalog No.</b>	<b>WX2021</b>
<b>UPC Code</b>	<b>4003019423231</b>
<b>Wattage</b>	<b>40 W &amp; 80 W</b>
<b>Soldering Pencil(s)</b>	<b>WXMP &amp; WXMT</b>
<b>Temperature Range</b>	<b>150° F to 850° F</b>
<b>Voltage Input/Output</b>	<b>120 V/24 V</b>
<b>Supplied Tip(s)</b>	<b>RT3 &amp; RTW3</b>
<b>Iron Stand</b>	<b>WDH50 &amp; WDH60</b>
<b>Temperature Accuracy</b>	<b>+/- 15° (9° C)</b>
<b>Packaging</b>	<b>Industrial Box/ Carton</b>
<b>Tech. Spec.</b>	<b><a href="#">Solder Safety Warnings.pdf</a></b>
<b>Low Res. Image</b>	<b><a href="#">WX2021_100.jpg</a></b>
<b>High Res. Image</b>	<b><a href="#">WX2021_300.jpg</a></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

### Package Details (Dimensions)

Email this Page

#### Product Features:

- Fine, thin WXMP soldering pencil is suited for work under a microscope
- WXMT tweezers are ideal for soldering and desoldering small SMD parts
- Capacitive glass touch screen is chemical and temperature resistant
- Turn and click wheel with enter key and finger guide is intuitive to use
- Multi-language menu navigation
- Large graphic LCD display can be viewed from all angles
- Versatile connectivity options - preheaters and fume extraction systems
- Multi-purpose USB port for parameter configuration and data logging
- ESD safe to protect sensitive components
- WXMP uses RT series tips, WXMT uses RTW series cartridges

**Erem**  
**4 1/4" Diagonal, Small Head Cutter, Super Full Flush Cut, Magic**



◀◀ previous print close next ▶▶

**Product Details**

<b>Catalog No.</b>	<b>632N</b>
<b>UPC Code</b>	<b>043127137051</b>
<b>Length (Inches)</b>	<b>4.25</b>
<b>Head Style/Cut Type</b>	<b>Oval/Super Full Flush</b>
<b>Max Cutting Diameter (Inches)</b>	<b>.040</b>
<b>Jaw Length (Inches)</b>	<b>.394</b>
<b>Head Width (Inches)</b>	<b>.394</b>
<b>Head Thickness (Inches)</b>	<b>.236</b>
<b>Application</b>	<b>Micro-electronics</b>
<b>Packaging</b>	<b>Industrial Box/Carton</b>
<b>Literature</b>	<b><a href="#">55647.pdf</a></b>
<b>Lineart</b>	<b><a href="#">55580772.pdf</a></b>
<b>Low Res. Image</b>	<b><a href="#">632N_100.jpg</a></b>
<b>High Res. Image</b>	<b><a href="#">632N_300.jpg</a></b>
<b>Stock Item</b>	<b>Normal Stock Item</b>

**Package Details (Dimensions)**

[Email this Page](#)

**Product Features:**

- **Small head, super full flush**