


PRODUCT DATA SHEET

Part Number: W503

Type	Size	Rating	Description
Incandescent	T10	6.5V 300mA	T-3¼ Miniature Edison Screw Lamp



Dimensions in millimetres

TEST VOLTS	CURRENT (mA)			LIGHT OUTPUT (Lm)			LIFE Hours
	Min.	Nom.	Max.	Min.	Nom.	Max.	
6.5	270	300	330	10	12	14	4000

Notes:

- 1 **Base Type** E10/13 (BS EN 60061-1)
- 2 **Filament Shape** C-2R
- 3 **LCL** 16mm nominal
- 4 **Bead colour** White or clear
- 5 **Lamp Marking** CML 6.5V 300mA
- 6 **Environmental** RoHS & REACH SVHC compliant