

Specification Sheet

Part Number: 111-01671



Aerial Support Tie, 12.4", PA66HIRHSUV, Black, 500/bag

Article Number

111-01671

Type

TAS120M

Color

Black (BK)

Features & Benefits

- UV resistant materials contain an inhibitor that prolongs the life of the tie in outdoor environments.
- One-piece design reduces installation time.
- Outside serrations prevent cable damage.

Quantity Per

bag

Product Description

Aerial Support Ties feature a built-in spacer to separate cables from the support wire and prevent abrasion. A one-piece design, combining the tie and spacer into one part, reduces installation time and inventory costs. The outside serrations along the strap prevent damage to cables. Formulated from a special nylon blend, these ties are specifically suited for long-term outdoor use. The bent tail allows for quick and simple installation by hand.

Short Description

Aerial Support Tie, 12.4", PA66HIRHSUV, Black, 500/bag

Global Part Name

TAS120M-PA66HIRHSUV-BK

Minimum Tensile Strength (Imperial)

120

Minimum Tensile Strength (Metric)

535

Length L (Imperial)

12.4

Length L (Metric)

270.0

Fixation Method

Others

Identification Plate Position

none

Releasable Closure

No

Tie Closure

plastic pawl

Variant

Outside Serrated

Width W (Imperial)

0.5

Width W (Metric)

12.7

Bundle Diameter Max (Imperial)

2.7

Bundle Diameter Max (Metric)

70.0

Thickness T (Metric)

1.58

Cable Tie Head Width (Imperial)

1.3

Height H (Imperial)

.76

Height H (Metric)	19.0
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)
Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
Operating Temperature (Metric)	-40°F to +230°F (-40°C to +110°C)
Reach Complaint(Article 33)	Yes
ROHS Complaint	Yes
Package Quantity(Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909987
Content Unit(BMEcat)	pcs.