

Han 28DD F-c



Part number	09 16 028 3101
Specification	Han 28DD F-c
HARTING eCatalogue	https://b2b.harting.com/09160283101

Identification

Category	Inserts
Series	Han DD [®]

Version

Termination method	Crimp termination
Gender	Female
Size	10 A
Number of contacts	28
PE contact	Yes
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.14 ... 2.5 mm ²
Rated current	10 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	3
Rated voltage acc. to UL	600 V
Rated voltage acc. to CSA	600 V
Insulation resistance	> 10 ¹⁰ Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500



Pushing Performance

Material properties

Material (insert)	Polycarbonate
Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0

Specifications and approvals

Specifications	EN 60664-1 IEC 61984
Approvals	DNV GL
UL / CSA	UL 1977 ECBT2.E235076

Commercial data

Packaging size	1
Net weight	37 g
Country of origin	China
European customs tariff number	85389099
eCl@ss	27440205 Contact insert for industrial connectors