


**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [5033980891](#)  
**Status:** **Active**  
**Overview:** [microSD Memory Card Connector](#)  
**Description:** 1.10mm Pitch microSD Memory Card Connector, Normal Mount Surface Mount, Push-Push Type, 1.28mm Height

**Documents:**

[3D Model](#) [Packaging Specification SPK-503398-001-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-503398-001-001 \(PDF\)](#)



*Series image - Reference only*

**General**

Product Family	Memory Card Sockets
Series	<a href="#">503398</a>
Overview	<a href="#">microSD Memory Card Connector</a>
Product Name	microSD Card
Style	Push-Push
UPC	883906688820

**Physical**

Card Detection Switch	Yes
Circuits (Loaded)	8
Color - Resin	Black
Durability (mating cycles max)	10000
Ejector Button Side	N/A
Material - Contact	Copper Alloy
Material - Plating Termination	Gold, Tin
Material - Shell	Stainless Steel
Net Weight	270.002/mg
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.10mm
Temperature Range - Operating	-25° to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.5A
Shielded	Yes
Voltage - Maximum	10V AC (RMS)/DC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	SPK-503398-001-001
Product Specification	PS-503398-001-001
Sales Drawing	SD-503398-001, SD-503398-001-001, SD-503398-002

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per  
-ED/88/2018 (15  
January 2019)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[503398 Series](#)

**Use With**

microSD Card