



# E2770SH

## 68.6cm (27") LCD MONITOR

Energy-saving LED backlighting, high contrast ratios and ultra-fast 1ms response time deliver clear, vibrant viewing without ghosting or blur. The convenient built-in speakers provide rich, clear sound.



AUDIO



HDMI



HEADPHONE OUT



TILT

### GENERAL FEATURES

|                          |                       |
|--------------------------|-----------------------|
| Line                     | Value-line            |
| Panel Type               | TN                    |
| Panel Size               | 27" / 68.6 cm         |
| Aspect Ratio             | 16:9                  |
| Brightness               | 300 cd/m <sup>2</sup> |
| Contrast Ratio Dynamic   | 20M:1                 |
| Contrast Ratio Static    | 1000:1                |
| Pixel Pitch(H) (V)       | 0.311                 |
| Display Area (H x V)     | 597.89x336.31         |
| Viewing Angle (CR >= 10) | 170/160               |
| Response time            | 1ms                   |
| Color                    | Black                 |

### SCANNING FREQUENCY

|                    |                  |
|--------------------|------------------|
| Scanning Frequency | 30-83khz/50-76hz |
| Pixel Frequency    | 148.5MHz         |

### RESOLUTION

|                        |                |
|------------------------|----------------|
| Maximum Resolution     | 1920x1080@60Hz |
| Recommended Resolution | 1920x1080@60Hz |
| Colors                 | 16.7 Million   |
| HDCP compatible        | Yes            |

### CONNECTORS

|             |     |
|-------------|-----|
| D-Sub       | Yes |
| DVI         | Yes |
| HDMI        | 1x  |
| USB         | -   |
| MHL         | -   |
| DisplayPort | -   |

### POWER

|                   |                                     |
|-------------------|-------------------------------------|
| Power Source      | 100 - 240V 50/60Hz                  |
| Power Consumption | On: 31W, Standby: 0.37W, Off: 0.15W |
| Zero Power Switch | -                                   |

### OTHER FEATURES

|                 |         |
|-----------------|---------|
| Plug and play   | Yes     |
| Kensington Lock | Yes     |
| i-Menu          | Yes     |
| e-Saver         | Yes     |
| Vesa Wallmount  | 100x100 |
| Speakers        | 2W      |

|             |  |
|-------------|--|
| Regulations | Energystar 6<br>TCO 6<br>EPEAT Gold<br>TUV-GS<br>TUV-Bauart<br>CE<br>FCC<br>EAC<br>PVC/BRF Free<br>ISO Certified Production<br>RoHS compliant<br>EUP compliant<br>Reach compliant<br>dicom_part_14 |
|-------------|--|

### ACCESSORIES

|                       |
|-----------------------|
| VGA Cable             |
| HDMI Cable            |
| Audio Cable           |
| Power Schuko C7 Cable |

### ERGONOMIC DATA

|       |        |
|-------|--------|
| Pivot | No     |
| Tilt  | -5/+15 |

### DIMENSIONS

|                            |   |
|----------------------------|---|
| Product with stand (W×H×D) | 642.4x449.3x241.9 mm                      |
| Packaging (W×H×D)          | 730x500x145 mm                            |
| Weight                     | 4.8 kg wo/packaging<br>6.8 kg w/packaging |
| Warranty                   | 3 Years                                   |
| EAN                        | 4038986185349                             |