



# U3277FWQ

## 80cm (31.5") LCD MONITOR

Featuring advanced AMVA panel technology, 4K UHD resolution, 95% NTSC colour gamut and a large 31.5-inch screen, this display is designed to impress demanding professionals.



SCREEN+



ZEROSWITCH



AUDIO



HDMI



MHL



DISPLAYPORT



TILT

### GENERAL FEATURES

Line	Pro-line
Panel Type	MVA
Panel Size	31.5" / 80 cm
Aspect Ratio	16:9
Brightness	350 cd/m <sup>2</sup>
Contrast Ratio Dynamic	80M:1
Contrast Ratio Static	3000:1
Pixel Pitch(H) (V)	0.1845
Display Area (H x V)	708 x 399
Viewing Angle (CR >= 10)	178/178
Response time	4ms GTG
Color	Black/Silver

### SCANNING FREQUENCY

Scanning Frequency	30~160KHz / 23~ 80Hz
Pixel Frequency	170Mhz

### RESOLUTION

Maximum Resolution	3840x2160@60hz
Recommended Resolution	3840x2160@60Hz
Colors	1.07 Billion
HDCP compatible	Yes

### CONNECTORS

D-Sub	Yes
DVI	Yes
HDMI	1x
USB	-
MHL	Yes
DisplayPort	1x

### POWER

Power Source	100 - 240V 50/60Hz
Power Consumption	On: 50W, Standby: 0.5W, Off: 0.5W
Zero Power Switch	Yes

### OTHER FEATURES

Plug and play	Yes
Kensington Lock	Yes
Multiview	Yes
i-Menu	Yes
e-Saver	Yes
Screen+	Yes
Vesa Wallmount	100x100

Regulations	Energystar 6 TCO 6 EPEAT Gold TUV-GS TUV-Bauart CE FCC EAC PVC/BRF Free ISO Certified Production RoHS compliant EUP compliant Reach compliant dicom_part_14
-------------	--

### ACCESSORIES

Displayport Cable
Power Schuko C13 Cable

### ERGONOMIC DATA

Pivot	No
Tilt	-5/+23

### DIMENSIONS

Product with stand (W×H×D)	741.88x516.9x178.2 mm
Packaging (W×H×D)	627x848x214 mm
Weight	8 kg wo/packaging 12.3 kg w/packaging
Warranty	3 Years
EAN	4038986185950