

# 32ML600M

32" Class Full HD IPS LED Monitor with HDR 10

EAN CODE: 8806098424740

32"

KEY FEATURES

- 32" FHD (1920 x 1080) IPS Display
- DCI-P3 95% Colour Gamut
- On Screen Control / Screen Split
- HDR 10
- On Screen Control
- Wall Mountable

For more information  
[www.lg.com/uk/monitors](http://www.lg.com/uk/monitors)



PRODUCT FEATURES

DISPLAY	
Size (Inch)	31.5 Inch
Size (cm)	-
Resolution	1920 x 1080
Panel Type	IPS
Aspect Ratio	16:9
Pixel Pitch	0.1212 x 0.3637mm
Brightness (Min.)	240 cd/m <sup>2</sup>
Brightness (Typ.)	300 cd/m <sup>2</sup>
Color Gamut (Min.)	DCI-P3 90% (CIE1976)
Color Gamut (Typ.)	DCI-P3 95% (CIE1976)
Color Depth (Number of Colors)	16.7M
Contrast Ratio (Min.)	700:1
Contrast Ratio (Typ.)	1200:1
Response Time	5ms (GtG at Faster)
Viewing Angle (CR≥10)	178°(R/L), 178°(U/D)
Surface Treatment	Haze 1%,3H,Anti-Glare Layer
SOUND	
Speaker	NO
Speaker_Output (unit)	N/A
Speaker_Channel	N/A
POWER	
Type	External Power(Adapter)
AC Input	100-240Vac, 50/60Hz
Power Consumption (Typ.)	36.7W
Power Consumption (Max.)	39W
Power Consumption (Energy Star)	NA
Power Consumption (Sleep Mode)	Less than 0.3W
Power Consumption (DC Off)	Less than 0.3W

CONNECTIVITY	
D-Sub	YES(1ea)
D-Sub (Max. Resolution at Hz)	1920 x 1080 at 75Hz
DVI	NO
DVI (Max Resolution at Hz)	NA
HDMI	YES(2ea)
HDMI (Max. Resolution at Hz)	1920 x 1080 at 75Hz
DisplayPort	NO
DP Version	N/A
DP (Max. Resolution at Hz)	N/A
Mini DisplayPort	NO
mDP Version	N/A
mDP (Max. Resolution at Hz)	N/A
Thunderbolt	NO
Thunderbolt(USB-C Compatiblity)	NO
Thunderbolt (Max. Resolution at Hz)	N/A
Thunderbolt (Data Transmission)	NO
Thunderbolt (Power Delivery)	N/A
USB-C	NO
USB-C (Max. Resolution at Hz)	N/A
USB-C (DP Alternate Mode)	NO
USB-C (Data Transmission)	NO
USB-C (Power Delivery)	N/A
Daisy Chain	NO
USB Upstream Port	NO
USB Downstream Port	NO
Audio In	NO
Mic In	NO
Headphone out	YES
Line out	NO

# 32ML600M

32" Class Full HD IPS LED Monitor with HDR 10

EAN CODE: 8806098424740

32"

KEY FEATURES

- 32" FHD (1920 x 1080) IPS Display
- DCI-P3 95% Colour Gamut
- On Screen Control / Screen Split
- HDR 10
- On Screen Control
- Wall Mountable

For more information  
[www.lg.com/uk/monitors](http://www.lg.com/uk/monitors)



PRODUCT FEATURES

FEATURES	
HDR 10	YES
VESA DisplayHDR™	NO
HDR Effect	YES
Nano IPS™ Technology	NO
Wide Color Gamut	YES
Color Calibrated	YES
HW Calibration	NO
Auto Brightness	NO
Flicker safe	YES
Reader Mode	YES
Color Weakness	YES
Super Resolution+	NO
1ms Motion Blur Reduction	NO
NVIDIA G-Sync™	NO
RADEON FreeSync™	NO
FreeSync (Low Frame Compensation)	NO
Black Stabilizer	YES
Dynamic Action Sync	YES
Crosshair	YES
Sphere Lighting	NO
PBP	NO
PIP	NO
Smart Energy Saving	YES
Camera	NO
Mic	NO

MECHANICAL	
Display Position Adjustments	Tilt
Wall Mountable	100 x 100 mm

DIMENSIONS /WEIGHT	
Dimension with Stand (W x H x D)	729.4 x 513.3 x 209.3 mm
Dimension without Stand (W x H x D)	729.4 x 430.3 x 45.0 mm
Dimension in Shipping (W x H x D)	813 x 516 x 150 mm
Weight with Stand	6.6 kg
Weight without Stand	6.2 kg
Weight in Shipping	9.2 kg

ACCESSORY	
D-Sub	NO
DVI-D	NO
HDMI	YES
Display Port	NO
mDP to DP	NO
Thunderbolt	NO
USB Type C	NO
USB Type C to A Gender	NO
USB A to B	NO
USB3.0 Upstream Cable	NO
PC Audio	NO
Remote Controller	NO
Others (Accessory)	-