



LG IPS Narrow Bezel Infinity Display Monitor

The Infinity Display provides a boarderless visual experience for 4-side of the display for an all-inclusive view.

For more information
www.lg.com/uk/monitors

SPECIFICATION

FEATURE

Size (Inch)	23.8"
Panel Type	IPS (Neo Blade III)
Colour Gamut (CIE1931)	sRGB over 99%
Colour Depth (Number of Colours)	16.7M Colours
Pixel Pitch (mm)	0.2745x0.2745
Aspect Ratio	16:9
Resolution	1920x1080
Brightness	250cd/m2
Contrast Ratio (Original)	1000:1
(DFC)	Mega
(GTG)	5ms
Surface Treatment	Anti Glare, 3H
Viewing Angle (CR≥10)	178/178

SPEAKER

Type	Slim Invisible Speaker
Audio Output (Watt)	5Wx2
Others	Maxx Audio

POWER


Type	Adaptor
Input	100~240Vac, 50/60Hz
Output	19V/1.7A
Normal On (EPA)	18W
Normal On (Typ.)	21W
Sleep Mode (Max)	0.3W
DC Off (Max)	0.3W

JACK INPUT/OUTPUT

D-Sub	Yes
DVI-D	-
Composite	-
S-Video	-
Component	-
SCART	-
CI Slot	-
HDMI	HDMIx2
DisplayPort	-
Signal Input Jack Location	Back
PC Audio In	Yes
Audio Input Jack Location	Back
Headphone Out	Yes
Line Out	-
Optical Out	-
Audio Output Jack Location	Back

FREQUENCY

D-Sub H-Frequency	30~83kHz
D-Sub V-Frequency	56~75Hz
DVI-D H-Frequency	-
DVI-D V-Frequency	-
HDMI H-Frequency	30~83kHz
HDMI V-Frequency	56~75Hz
DisplayPort H-Frequency	-
DisplayPort V-Frequency	-



For more information
www.lg.com/uk/monitors

SPECIFICATION

OSD

Country	English, Germanic, French, Spanish, Italian, Swedish, Finnish, Portuguese, Polish, Russian, Greek, Chinese, Japanese, Korean, Ukrainian, Portuguese (Brazil), Hindi
Number of Language	17

SPECIAL FEATURE

Picture Mode	Custom, Reader 1, Reader 2, Photo, Cinema, Game, Colour Weakness
Reader Mode	Yes
Original Ratio	Yes
DDC/CI, HDCP	Yes
Intelligent Auto (Auto Adjustment)	Yes
Key Lock	Yes
Plug & Play	Yes
Response Time Control	Yes
Colour Calibrated	Yes
Flicker Safe	Yes
Automatic Standby	Yes
Six Axis Control	Yes
Smart Energy Saving	Yes
Super Resolution+	Yes
4 Screen Split	Yes
OnScreen Control	Yes
Others	Black Stabilizer

COLOUR

Front	Silver Spray
Back Cover	White
Stand	Silver Spray
Base	Silver Spray

STAND

Base Detachable	Yes
Tilt (Angle)	-2°~15°

SIZE (MM)

Set (With Stand)	W541 x D186.2 x H414.5
Set (Without Stand)	W541 x D46.6 x H313.3
Box	610x380x125
Wall Mount	75x75

WEIGHT (KG)

Set (With Stand)	3.2kg
Set (Without Stand)	2.9kg
Box	4.7kg

STANDARD

UL(cUL)	Yes
TUV-TYPE	Yes
FCC-B, CE	Yes
EPA 6.0	Yes
ErP	Yes
Windows	Win10

ACCESSORY

Power Cord, D-Sub, HDMI	Option
Stand Body	Yes
Stand Base	Yes
Cable Holder, Stand Cover	Yes
Screw (2EA)	Yes
CD, ESG	Yes
Manual	Yes