



4.50W

VT-5015 4.5W WIFI GU10 SPOTLIGHT-COLOR CHAGEABLE COMPATIBLE WITH ALEXA AND GOOGLE HOME

Equivalent 35W	Lumens 360	Beam Angle 100	Dimensions 50x70mm
--------------------------	----------------------	--------------------------	------------------------------

3 IN 1
 SKU:8436

2 YEARS
 WARRANTY



Technical Information

EQ-WATTS: 35	LED Chip Type: SMD
Watts: 4.5000	IP Rating: IP20
Lumens: 360	Dimmable: Yes
Holder Type: GU10	Warranty (Years): 2
Beam Angle: 100	CRI: >80
Unit Color: White	Operation Temperature: -20°C to +45°C
Body Type: Plastic	Input Power: AC:220-240V,50Hz
Long life: 20,000 Hours	Wireless Frequency: 2.4GHz

Features

- ✓ Perfect replacement for traditional HPS and MH Streetlights
- ✓ High Power LED Samsung Chip
- ✓ Uniformity in Light Distribution – Maximizes Efficiency
- ✓ Integrated IC driver
- ✓ Long Life span of 50,000 Hours - Low Maintenance - Energy Saving
- ✓ Reduced Utility cost by space to height alignment
- ✓ Dedicated IP65 Sealed Optical Cavities
- ✓ Reduced CO² emissions
- ✓ Applications - Streets, Industrial Facilities, Cross Roads and many more

Note: 

Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

Packaging

Unit Details

Gross Weight(GW) Kgs	0.047
Unit CBM	0.00034

Listing Details

EAN Code	3800157641326
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	100
---------------------------------	-----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES