



# Einhell

# EXPERT



Cordless Mitre Saw

**TE-MS 18/210 Li - Solo**

**Item No.: 4300890**

Ident No.: 11017

Bar Code: 4006825628074

## Features & Benefits

- Member of the Power X-Change family
- Boundless reach of action, no annoying cable, nothing to wind
- Compact, light construction and handle for easy transportation
- Turntable with precise angle setting for angular cuts
- Saw head tilts to the left and right for miter cutting
- X-Tend work supports with ergonomic singlehand operation facility
- High-grade precision saw blade, developed for cordless mitre saws
- Laser and LED for easy and safe use
- Clamping device for holding the workpiece securely in position
- Includes sawdust bag to keep the workplace clean
- Recommendation for best results: 2.6 Ah Plus battery or higher




## Technical Data

- |                                |                        |
|--------------------------------|------------------------|
| - No-load speed ( idle speed ) | 3000 min <sup>-1</sup> |
| - Saw blade                    | Ø210 x Ø30 mm          |
| - Number of teeth              | 40 Pieces              |
| - Mitre cut                    | 45 ° - 0 °             |
| - Swivelling range             | 47 ° - 47 °            |
| - Cutting capacity 90° x 90°   | 120 x 60 mm            |
| - Cutting capacity 90° x 45°   | 83 x 60 mm             |
| - Cutting capacity 45° x 90°   | 120 x 34 mm            |
| - Cutting capacity 45° x 45°   | 80 x 34 mm             |
| - Diameter of suction adapter  | 36 mm                  |



## Logistic Data

- |                                      |                    |
|--------------------------------------|--------------------|
| - Product weight (kg)                | 7                  |
| - Gross weight (kg)                  | 9.23               |
| - Dimensions single packaging        | 540 x 355 x 300 mm |
| - Pieces per export carton           | 1 Pieces           |
| - Gross weight of export carton      | 9.9 kg             |
| - Dimensions export carton           | 540 x 380 x 340 mm |
| - Container quantity (20"/40"/40"HC) | 384   780   1040   |



## Available as special accessories



18V 1,5Ah PXC Starter Kit  
PXC-Starter-Kit  
Item No.: 4512021  
Bar Code: 4006825601350  
Einhell Accessory



18V 2,0 Ah Power-X-Change  
Battery  
Item No.: 4511395  
Bar Code: 4006825610369  
Einhell Accessory



18V 2,0Ah PXC Starter Kit  
PXC-Starter-Kit  
Item No.: 4512040  
Bar Code: 4006825613681  
Einhell Accessory



18V 4,0Ah PXC Starter Kit  
PXC-Starter-Kit  
Item No.: 4512042  
Bar Code: 4006825613704  
Einhell Accessory



18V 30min Power-X-Change  
PXC-Charger  
Item No.: 4512011  
Bar Code: 4006825587029  
Einhell Accessory



18V 3,0 Ah Power-X-Change  
Battery  
Item No.: 4511341  
Bar Code: 4006825590593  
Einhell Accessory



18V 4,0 Ah Power-X-Change  
Battery  
Item No.: 4511396  
Bar Code: 4006825610376  
Einhell Accessory



18V 3,0Ah PXC Starter Kit  
PXC-Starter-Kit  
Item No.: 4512041  
Bar Code: 4006825613698  
Einhell Accessory



18V 2,6Ah P-X-C Plus  
Battery  
Item No.: 4511436  
Bar Code: 4006825616590  
Einhell Accessory



18V 5,2 Ah P-X-C Plus  
Battery  
Item No.: 4511437  
Bar Code: 4006825616606  
Einhell Accessory