

# KAE1H

operating head 45 x 45 mm - black color - black handle - blank for engraving



## Main

Range of product	Harmony Series K
Product or component type	Cam switch operating head
Component name	KAE
Product compatibility	Rear mounting bodies 12 and 20 A by 4 holes
Cam switch head type	With front plate 45 x 45 mm
Type of operator	Black handle, length = 35 mm
Rotary handle padlocking	Without
Presentation of legend	With mat black legend

## Complementary

Mechanical durability	1000000 cycles
CAD overall width	45 mm
CAD overall height	45 mm
CAD overall depth	60 mm
Length	35 mm
Product weight	0.029 kg

## Environment


protective treatment	TC
ambient air temperature for operation	-25...55 °C
ambient air temperature for storage	-40...70 °C
shock resistance	30 gn conforming to IEC 68-2-27
vibration resistance	5 gn, 10...150 Hz conforming to IEC 68-2-6
IP degree of protection	IP40 conforming to IEC 529 IP40 conforming to NF C 20-010

## Contractual warranty

Warranty period	18 months
-----------------	-----------

## Operating Head

For 4 Hole, Rear Mounting Body



## Operating Head

Panel Cut-out

