

XZCRV1511064D2

jumper cable XZ - male straight M12 5 pin - female straight M12 5 pin - PVC 2m



Main

Accessory / separate part category	Cabling accessory
Accessory / separate part type	Jumper cable

Complementary

Jumper cable end 1	M12 male, :5 pins (straight), fixing: screw-on
Jumper cable end 2	M12 female, :5 pins (straight), fixing: screw-on
Collar material	Metal
Cable composition	5 x 0.25 mm ²
Cable length	2 m
Wire insulation material	PVC
Cable outer diameter	5.2 mm
[Ue] rated operational voltage	250 V AC 300 V DC
[In] rated current	3 A
Insulation resistance	>= 1000 MOhm
Resistance across terminals	<= 5000 mOhm
Product weight	0.1 kg

Environment


IP degree of protection	IP65 IP67
product certifications	CULus
ambient air temperature for operation	-25...80 °C (static)
ambient air temperature for storage	-25...80 °C

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------

Dimensions

mm
in.



L : Length of cable

Connections and Schemes

