



### Main

Range of product	Harmony 9001K
Product or component type	Pilot light
Device short name	K

### Complementary

Bezel material	Chromium plated metal
Mounting diameter	30 mm
Lens type	Fresnel (plastic)
Cap/operator or lens colour	Red
Light source	Incandescent
Bulb base	BA 9s
Light block supply	Via transformer (f = 50/60 Hz) Via integral transformer (f = 50/60 Hz)
Connections - terminals	Screw clamp terminals (1 x 0.22...2 x 1.5 mm <sup>2</sup> ) conforming to IEC 60947-1
Shape of screw head	Round head
Operating position	Any position
[Us] rated supply voltage	110...120 V AC
Operating mode	Normal
Device presentation	Complete product

### Environment

product certifications	CE CSA LR25490 class 3211 03 UL listed file E42259 CCN NKCR
NEMA degree of protection	NEMA 1/2/3/3R/4/6/12/13

### Offer Sustainability

Sustainable offer status	785901094579
RoHS (date code: YYWW)	Compliant - since 0921 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold