

XVLA134

pilot light Ø8 - IP40 - red - protruding LED included - 24V - faston



Main

| | |
|---------------------------|--|
| Range of product | Harmony XVL |
| Product or component type | LED pilot light with black bezel |
| Component name | XVL |
| Mounting diameter | 8 mm |
| Light source | Protruding LED |
| Light block colour | Red |
| Protection type | Integral ballast resistor Built-in by diode |
| [Us] rated supply voltage | 24 V |
| IP degree of protection | IP40 conforming to IEC 60529 IP40 conforming to NF C 20-010 |

Complementary

| | |
|-------------------------------|--|
| Supply circuit type | DC |
| Connections - terminals | Tag for soldering connectors Tag for Faston connectors : 2.8 x 0.5 mm |
| Current consumption | 18 mA |
| [Ui] rated insulation voltage | 50 V conforming to IEC 60947-1 |
| Bulb lifespan | >= 100000 h |
| Nominal voltage limit | 0.8...1.1 Un |
| Terminals description ISO n°1 | (X1-X2)PL |
| Height | 12 mm |
| Width | 12 mm |
| Depth | 34 mm |
| Product weight | 0.003 kg |

Environment


| | |
|---------------------------------------|--|
| product certifications | CSA UL |
| protective treatment | TC |
| ambient air temperature for operation | -25...70 °C |
| ambient air temperature for storage | -40...70 °C |
| overvoltage category | Class 3 conforming to IEC 60536 Class 3 conforming to NF C 20-030 |

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

LED Pilot Light

Dimensions




(1) Tags for Faston connectors or soldered connections

e panel thickness: 1 to 8 mm/0.03 to 0.31 in.

| C | | Ø | |
|----|------|----|------|
| mm | in. | mm | in. |
| 32 | 1.26 | 12 | 0.47 |

LED Pilot Light

Panel Drilling



| Ø min | | G min | | H min | |
|-------|------|-------|------|-------|------|
| mm | in. | mm | in. | mm | in. |
| 8.2 | 0.32 | 12.5 | 0.49 | 12.5 | 0.49 |