




Screw-plug-connector 2,5 mm², 2 - 12-poles, with 3 flat plugs 6,3 x 0,8 each pole

Casing : polyamide
Screw : M 4 zinc-plated steel
Connecting body : zinc-plated steel


This connector is available in 2 - 12--pole and with earth-bracket. The labelling of the poles can be made according to your requirements. Delivery will be effected ready for installation with slightly twisted screws which are protected against self-loosening in the insulation-part.

This connector is available in other thermoplastic materials and colours.

Also available with glow wire resistance 750°C, flame < 2 sec. (IEC/EN60335-1).



24A 450V	PTI 250	T110	1mm ² -2.5mm ²	1mm ² -2.5mm ²	L=6mm-6.5mm
---------------------------	---------	------	--------------------------------------	--------------------------------------	-------------



No. of poles	Length	Article-no.	Fixing	Colour	kg/100 pcs.	Pkg. qty.
2	27,00	1196300402	screw-fixing	grey	1,20	250
3	42,50	1196300403	screw-fixing	grey	1,80	200
4	58,00	1196300404	screw-fixing	grey	2,40	200
5	73,50	1196300405	screw-fixing	grey	3,00	100
6	89,00	1196300406	screw-fixing	grey	3,60	100
7	104,50	1196300407	screw-fixing	grey	4,20	50
8	120,00	1196300408	screw-fixing	grey	4,80	50
9	135,50	1196300409	screw-fixing	grey	5,40	50
10	151,00	1196300410	screw-fixing	grey	6,00	50
11	166,50	1196300411	screw-fixing	grey	6,60	50
12	182,00	1196300412	screw-fixing	grey	7,20	20

