



Main

Range of product	Harmony XAW
Product or component type	Complete control station
Device short name	XAWF
Control station application	Start function
Material	Metal
Control station composition	1 flush push-button, green spring return 1 NO

Complementary

Colour of base of enclosure	Black
Colour of cover	Black
Cable entry	1 entry for ISO M20 cable gland
Width	80 mm
Depth	77 mm
Height	80 mm
Marking	Ex tb IIIC T85°C Db IP65
Mechanical durability	5000000 cycles
Short-circuit protection	10 A cartridge fuse type gG
[Ie] rated operational current	3 A at 240 V AC-15, A600 conforming to EN/IEC 60947-5-1 6 A at 120 V AC-15, A600 conforming to EN/IEC 60947-5-1 0.1 A at 600 V DC-13, Q600 conforming to EN/IEC 60947-5-1 0.27 A at 250 V DC-13, Q600 conforming to EN/IEC 60947-5-1 0.55 A at 125 V DC-13, Q600 conforming to EN/IEC 60947-5-1 1.2 A at 600 V AC-15, A600 conforming to EN/IEC 60947-5-1

Environment

ambient air temperature for operation	-20...60 °C
overvoltage category	I conforming to IEC 60536
IP degree of protection	IP65 IEC 60529
standards	EN/IEC 60947-5-1 EN/IEC 60947-1 EN 61000-6-2 EN 60079-0 : 2009 EN 60079-31 : 2009 IEC 60079-0 : 2007 IEC 60079-31 : 2008 EN 60947-5-4
directives	94/9/EC - ATEX directive
dust zone	Zone 21 - 22
product certifications	INERIS 04ATEX0023X

Contractual warranty

Warranty period	
-----------------	--