



### Main

|                           |                        |
|---------------------------|------------------------|
| Range of product          | Harmony 9001K          |
| Product or component type | Selector switch        |
| Device short name         | K                      |
| Type of operator          | Maintained             |
| Operator profile          | Black gloved hand knob |

### Complementary

|                               |  |
|-------------------------------|--|
| Bezel material                | Chromium plated metal  |
| Mounting diameter             | 30 mm  |
| Operator position information | 2 positions  |
| Connections - terminals       | Screw-clamp terminals 1 x 0.22...2 x 1.5 mm <sup>2</sup> IEC 60947-1 |
| Device presentation           | Complete product   |

### Environment

|                           |   |
|---------------------------|---|
| NEMA degree of protection | NEMA 1/2/3/3R/4/6/12/13   |
| product certifications    | CE<br>UL listed file E42259 CCN NKCR<br>CSA LR24590 class 3211 03 |

### Offer Sustainability

|                          |   |
|--------------------------|---|
| Sustainable offer status | 785901398486  |
| RoHS (date code: YYWW)   | Compliant - since 0921 - Schneider Electric declaration of conformity |
| REACH                    | Reference not containing SVHC above the threshold                     |