

XCRZ04

limit switch lever XCRZ - steel square rod 6 mm,
L=300 mm



Main

Range of product	OsiSense XC
Series name	Special format
Product or component type	Limit switch lever
Device short name	XCRZ
Product compatibility	XCRA XCRB
Movement of operating head	Rotary
Type of operator	Square rod metal square rod 6 mm, L = 300 mm
Switch actuation	By any moving part
Type of approach	Lateral approach
Positive opening	With

Complementary

Associated complete product	XCRA11 XCRA12 XCRA15 XCRA51 XCRA52 XCRA55 XCRB11 XCRB12 XCRB15 XCRB51 XCRB52 XCRB55
Product weight	0.029 kg

Environment

ambient air temperature for operation	-25...70 °C
---------------------------------------	-------------

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0903 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.