

XAPG1201

die-cast empty control station - XAP-G - Ø 22 -
80x80mm front plate - 1 cut-out



Main

Range of product	Harmony XAP
Product or component type	Die-cast empty control station
Device short name	XAPG
Product destination	For Ø 22 mm control and signalling units
Product front plate size	80 x 80 mm
Usable depth	49 mm
Number of cut-out	1 cut-out
Colour of base of enclosure	Grey RAL 7032
Colour of cover	Grey RAL 7032
Material	Zinc alloy
Cable entry	1 hole with blanking plug for cable gland with <= 14 mm 1 hole without blanking plug for cable gland with <= 14 mm
Product mounting	Flush mounting
IP degree of protection	IP65 conforming to IEC 60529 IP657 conforming to NF C 20-010

Complementary

Number of vertical rows	1
Product weight	0.455 kg

Environment

protective treatment	TC
ambient air temperature for storage	-40...70 °C
ambient air temperature for operation	-25...70 °C
electrical shock protection class	Class I conforming to IEC 60536 Class I conforming to NF C 20-030

Contractual warranty

Warranty period	18 months
-----------------	-----------