


XACS399

single isolating block XACS - for power circuit -
horizontal fixing centres-40mm



Main

Range of product	Harmony XAC
Product or component type	Isolating block
Component name	XACS
Electrical circuit type	Power circuit
Contact block application	Emergency stop push-button
Contact block type	Single
Product compatibility	XACB
Contacts type and composition	3 NC
Mounting of block	Front mounting
Contact operation	Snap action

Complementary

Connections - terminals	Screw clamp terminals, connection capacity: 1 x 2.5 mm ² with or without cable end Screw clamp terminals, connection capacity: 2 x 1.5 mm ² with or without cable end
Horizontal fixing centres	40 mm
Mechanical durability	1000000 cycles
Contact code designation	A300 AC-15, U _e = 240 V, I _e = 3 A conforming to IEC 60947-5-1 appendix A Q300 DC-13, U _e = 250 V, I _e = 0.27 A conforming to IEC 60947-5-1 appendix A
[Ui] rated insulation voltage	400 V (degree of pollution: 3) conforming to IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to IEC 60947-1
Rated operational power in W	3000 W AC-23B at 400 V
Product weight	0.1 kg

Environment

standards	EN 60947-3 IEC 60947-3 CSA C22.2 No 14
ambient air temperature for operation	-25...70 °C
ambient air temperature for storage	-40...70 °C
vibration resistance	15 gn (f = 10...500 Hz) conforming to IEC 60068-2-6
shock resistance	100 gn conforming to IEC 60068-2-27
electrical shock protection class	Class II conforming to IEC 61140

Contractual warranty

Warranty period	18 months
-----------------	-----------