

Main

Accessory / separate part category	Cabling accessories
Accessory / separate part type	Connector
Electrical connection	Straight female connector M23, 19 pins
Collar material	Metal
Status LED	Without
Cable connection	Solder terminal / wire size $\leq 1 \text{ mm}^2$ / clamping capacity 9...12 mm

Complementary

Cable gland type	Pg 13.5
Cable connector fixing	Screw-on
[Ue] rated operational voltage	60 V AC 75 V DC
[In] rated current	7.5 A
Enclosure material	Metal
Insulating resistance	$> 10000000 \text{ G}\Omega$
Contact resistance	$\leq 5000 \mu\text{Ohm}$
Product weight	0.08 kg

Environment

IP degree of protection	IP65
ambient air temperature for operation	$-25 \dots 110 \text{ }^\circ\text{C}$


Offer Sustainability

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be Compliant on 4Q2013 Will be Compliant on 4Q2013

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions



(1) Cable gland: no. 13 metal (Pg 13.5)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections and Schemes

