

Stripping diagonal cutters Professional electric with DynamicJoint®



Z 14 0 06

Order-No.	mm	II	✂	Ømm	SB	📦
26745	160	6 ½	13	1.6		5
27431	160	6 ½	13	1.6	x	5

DIN ISO 5749. Manufactured acc. to IEC 60900.

BiCut® Professional electric high-performance diagonal cutters with DynamicJoint®



Switchable

Z 18 0 06

Order-No.	mm	II	✂	Ømm	SB	📦
38191	200	8	21	3		5
38984	200	8	21	3	x	5

Manufactured acc. to IEC 60900.

Diagonal cutters Professional electric with DynamicJoint®



Z 12 0 06

Order-No.	mm	II	✂	Ømm	SB	📦
26737	140	5 ½	16	1.4		5
27428	140	5 ½	16	1.4	x	5
26741	160	6 ½	16	1.6		5
27429	160	6 ½	16	1.6	x	5
26744	180	7	17	1.8		5
27430	180	7	17	1.8	x	5

DIN ISO 5749. Manufactured acc. to IEC 60900.

Industrial electric diagonal cutters with DynamicJoint®



Z 12 0 09

Order-No.	mm	II	✂	Ømm	SB	📦
38633	140	5 ½	16	1.4		5
38860	140	5 ½	16	1.4	x	5
33177	160	6 ½	16	1.6		5
38861	160	6 ½	16	1.6	x	5

DIN ISO 5749. Manufactured acc. to IEC 60900.

INFOBOX:  
DynamicJoint®



Wiha DynamicJoint® – A new dimension in strength and durability

- Innovative: Optimised joint construction.
- Effective: Minimal power loss means less force needed for cutting.
- Permanent: Optimal performance even after thousands of cuts.