

Industrial lineman's pliers with DynamicJoint®



with extra long cutting edge

Z 02 2 02

Order-No.	mm	mm	mm	mm	SB	
40927	250	10	20	2.5		5
41219	250	10	20	2.5	x	5

Classic lineman's pliers with DynamicJoint®



with extra long cutting edge

Z 02 2 01

Order-No.	mm	mm	mm	mm	SB	
40709	250	10	20	2.5		5
41218	250	10	20	2.5	x	5

Inomic® electric combination pliers



Z 01 0 16

Order-No.	Typ	mm	mm	
33261	180	12	1.6	5

Manufactured acc. to IEC 60900.

Needle nose pliers Inomic® VDE




Z 06 0 16

Order-No.	Typ	mm	mm	
33259	160	12	1,6	5

Manufactured acc. to IEC 60900.

INFOBOX: Wiha Inomic®



Innovative and ergonomic.

- The angled shape of the Inomic® pliers enables work which is kind on the hands and muscles and is therefore recommended by doctors and therapists from the AGR.
- Improved grip control due to highly sensitive opening spring.
- Like an extension of your own hand: gripping is simple, firm and safe.
- Pliers can be transported and stored in a closed position, thanks to a locking mechanism.

