

R18DD3-120S | 18V Cordless Drill/Driver (1x2.0Ah)



- Cordless drill driver ideal for drilling in wood or metal and screw driving applications.
- 13mm ratcheting chuck for improved bit gripping strength and durability.
- 2 gears to control the max speed to match different materials and applications.
- 24 torque settings help to drive screws flush every time.
- LED lights up your work area for better visibility.

	R18DD3-120S
Battery pack capacity (Ah)	2.0
Battery type	Li-ion
Charger included?	Yes
Charging time	60
Chuck capacity (mm)	13
Max drilling steel (mm)	13
Max. drilling wood (mm)	38
Max. torque (Nm)	50
No load speed (rpm)	0-500 / 0-1800
No. of batteries supplied	1
Power	18V
Sound power level [dB(A)]	86.9
Sound power level uncertainty [dB(A)]	3.0
Sound pressure level (dB(A))	75.9
Sound pressure level uncertainty [dB(A)]	3.0
Supplied in	Tool bag
Torque settings	24
Weight [without battery] [Kg]	1.3
Weight with battery pack (kg)	1.7