

## R18PD5-120G | 18V Cordless Brushless Percussion Drill (1x2.0Ah)



- Brushless percussion drill ideal for drilling in wood or metal, driving screws or even drilling in masonry thanks to the hammer function.
- Ryobi's Brushless technology uses patented electronics to deliver more runtime and power.
- e-Torque™ control automatically drives screws flush for a perfect finish every time.
- 13mm ratcheting chuck for improved bit gripping strength and durability.
- 2 gears to control the max speed to match different materials and applications.
- LED lights up your work area for better visibility.

R18PD5-120G	
Battery pack capacity (Ah)	2.0
Battery type	Li-ion
Charger included?	Yes
Charging time	70
Chuck capacity (mm)	13
Max drilling steel (mm)	13
Max. drilling masonry (mm)	13
Max. drilling wood (mm)	32
Max. percussion rate (bpm)	6800 / 23800
Max. torque (Nm)	50
No load speed (rpm)	0-400 / 0-1400
No. of batteries supplied	1
Power	18V
Sound power level [dB(A)]	94.5
Supplied in	Recyclable Carton
Torque settings	Automatic
Weight [without battery] [Kg]	1.1
Weight with battery pack (kg)	1.5