

RBV3000CSV | 3000W Electric Blower Vac, Conversion Style



- Powerful 3000W motor.
- Conversion blower and vacuum with easy-to-remove tubes to convert quickly from blower mode to vacuum mode.
- Two-speed dial provides maximum airflow speed of 375km/h with quiet mode.
- Ultimate blower performance with 14 m³/min air volume.
- PowerMulching™ heavy duty metal blade offers 16:1 mulching ratio for better composting.
- Vertebrae™ shoulder strap provides maximum comfort to the user and balances the tool.

RBV3000CSV	
Air volume (m ³ per minute)	14
Airflow speed (km/h)	375
Collection bag capacity (l)	45
Mulching ratio	16:1
Power	3000W
Sound Power [dB Lwa]	106.0
Sound power level [dB(A)]	108
Sound power level guaranteed [dB(A)]	110
Sound power level uncertainty [dB(A)]	2
Sound pressure level (dB(A))	92.5
Sound pressure level uncertainty [dB(A)]	2
Supplied in	Recyclable Carton
Variable speed	No
Vibration level [m/s ²]	4.6
Vibration Level Auxiliary Handle [m/s ²]	3.9
Vibration Level Main Handle [m/s ²]	4.4
Vibration uncertainty [m/s ²]	1.5
Weight (kg)	4.2