



### Main

Range of product	9007
Series name	Heavy duty
Product or component type	Limit switch lever
Device short name	9007C
Associated head	9007B 9007T5 9007T10 9007A 9007N 9007C
Associated complete product	9007C 9007AW
Movement of operating head	Rotary
Type of operator	Steel spring return spring rod lever length: 12 in - offset: - -
Type of approach	Lateral approach
Positive opening	Without

### Complementary

Switch actuation	By any moving part
Product weight	0.1 lb(US)

### Environment

Ambient air temperature for operation	-20...185 °F
Ambient air temperature for storage	-20...185 °F
Environmental characteristic	Standard environment

### Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - Schneider Electric declaration of conformity

 [Schneider Electric declaration of conformity](#)

REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

[Contractual warranty](#)

Warranty period	18 months
-----------------	-----------