



Main

Range of product	OsiSense XU
Series name	Application assembly
Specific application of photoelectric detector	Object
Sensor name	XUD

Complementary

Electronic sensor type	Photo-electric sensor
Sensor design	Fiber design
Enclosure material	PBT
Wiring technique	3-wire
Supply circuit type	DC
Type of output signal	Discrete
Output type	Solid state
Discrete output function	1 NO or 1 NC programmable
Discrete output type	PNP
Electrical connection	Cable
Cable length	2 m
Cable material	PVC
Status LED	1 LED red instability 1 LED yellow output state
[Us] rated supply voltage	12...24 V DC reverse polarity protection
Supply voltage limits	10.8...26.4 V DC
Current consumption	<= 50 mA (no-load)
Switching capacity in mA	<= 100 mA overload protection <= 100 mA short-circuit protection
Voltage drop	<= 2 V closed
Switching frequency	<= 1 kHz
Add on output	Without
Delay first up	< 120 ms
Delay response	< 0.5 ms
Delay recovery	< 0.5 ms

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product compatibility	Glass or plastic fibre optics 1 mm or 2.2 mm
Setting-up	Sensitivity adjustment with teach mode
Lens material	PMMA
Depth	10 mm
Height	65 mm
Width	40 mm
Product weight	0.04 kg

Environment

Emission	Red
Interference protection	Without
Product certifications	CE cULus
IP degree of protection	IP64 IEC 529 optic fiber Ø 1 mm IP65 IEC 529 optic fiber Ø 2 mm
Ambient air temperature for operation	-10...55 °C
Ambient air temperature for storage	-30...70 °C
Vibration resistance	7 gn 10...55 Hz) IEC 60068-2-6 +/-0.5 mm 10...55 Hz) IEC 60068-2-6
Shock resistance	30 gn (duration = 11 ms) conforming to IEC 60068-2-27

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0623 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------