



9W

VT-5010 9W A60 BULB COMPATIBLE WITH AMAZON ALEXA AND GOOGLE  
 HOME COLORCODE:RGB+6000K E27

Lumens <b>800</b>	Beam Angle <b>200</b>	Dimensions <b>60x112mm</b>
----------------------	--------------------------	-------------------------------

SKU:7452



**2 YEARS**  
 WARRANTY



## Technical Information

Watts: 9	Long life: 20,000 Hours
Lumens: 800	LED Chip Type: SMD
Holder Type: E27	IP Rating: IP20
Shape: A60	Dimmable: Yes
On/Off Cycles: >20000	Warranty (Years): 2
Beam Angle: 200	PF: >0.5
Unit Color: White	CRI: >80
Body Type: Thermoplastic	Operation Temperature: -25 to +50°C
Energy Rating: A+	Input Power: AC:85-265V 50/60Hz



## Features

- ✓ V-TAC Smart A60 Thermoplastic Bulb designed with Wifi 2.GHz
- ✓ Control the light with V-TAC Smart app(Offering multiple functions - Color Changing, Dim, On/Off)
- ✓ Wireless Standard IEEE 802.11 b/g/n
- ✓ Switching cycle of 20,000 times
- ✓ Compatible with Alexa and Google Home
- ✓ Applications: Perfect for Residential, Commerical, Hotels and many other applications



Note: Suitable & Recommended for maximum daily use of 10-12 hours, usage beyond this would void the warranty

## Packaging

### Unit Details

Gross Weight(GW) Kgs	0.175
Unit CBM	0.000775

### Listing Details

EAN Code	3800157637817
Commodity Code	9405403990

### Master Box Packaging

Master Box Qty (Pcs Per Carton)	60
---------------------------------	----

READY STOCKS IN  
**UK & EU**



Dispatch within  
**24** Hours

[www.vtacexports.com](http://www.vtacexports.com)

OUR PRODUCTS ARE  
CURRENTLY SOLD IN OVER  
**70**  
COUNTRIES