



Part Number: HP7 PLUS

Description: Flashlight

A perfect mix of size, form, and performance, the HP7 Flashlight is rightfully one of our most popular handheld lights. It combines our Pure Beam Focusing System with Slide Focus with a high, medium, and low output modes to illuminate with either a super wide flood beam or spot mode with transition halo at varying distances and brightness all controllable with one hand. Its anti-roll tail cap allows you to set it on uneven surfaces without rolling off and it even allows you to stand the light upon its cap for vertical lighting situations.

With Coast's commitment to quality, the HP7 Flashlight is impact resistant, weather resistant and its LED is virtually unbreakable. The HP7 Flashlight is backed by Coast's lifetime warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.



Specifications:

- **BATTERY TYPE:** 4 x AAA (Alkaline)
- **BEAM DISTANCE (HIGH):** 751 ft / 229 m
- **BEAM DISTANCE (LOW):** 288 ft / 88 m
- **BEAM DISTANCE (MEDIUM):** 544 ft / 166 m
- **INCLUDED:** 4 x AAA Batteries
- **LENGTH:** 5.6 in / 14.2 cm

- **LIGHT OUTPUT (HIGH):** 410 Lumens
- **LIGHT OUTPUT (LOW):** 60 Lumens
- **LIGHT OUTPUT (MEDIUM):** 215 Lumens
- **RUNTIME (HIGH):** 2 h

- **RUNTIME (LOW):** 12 h
 - **RUNTIME (MEDIUM):** 6 h 30 min
 - **WEIGHT:** 7.2 oz / 204 g
-

Features:




• **BEAM LOCK**

Set the beam to stay how you like it. COAST Beam Lock technology makes our Slide Focusing system even more valuable, with the option to lock the beam in place on spot, flood, or anywhere in between. Twisting the head of the light to the left locks the beam in place, and twisting it back to the right releases the slide mechanism back into motion.



• **HIGH|MEDIUM|LOW**

Control your light power with the push of a button. Cycle between full light, medium light and low light options.



PURE-BEAM FOCUSING OPTIC

Pack two powerful beams into one and seamlessly transition—with no halos or hot spots—between short and long-range viewing. COAST's patented focusing technology adapts to your need. The Ultra View Flood beam delivers edge-to-edge clarity in a broad circle of light up to 11.5 feet / 3.5 meters across, and the Bulls-Eye Spot beam sends a sharp ray of light at a distance of up to 1151 feet / 351 meters, with a transitional halo around the spot to increase the effective viewing area.



SLIDE FOCUS

One-handed beam control. COAST's Slide Focus system enables you to seamlessly transition between spot and flood beam with the push or pull your finger. Responsive beam-shape control allows you to operate your light with a single hand and keep the other hand free.



WATER RESISTANCE

Don't worry about the weather. COAST lights that have passed the IPX4-level water resistance test are splash-resistant and built with durable materials that stand up to nature.