

## Han M23 HBM back 2,7mm



|                    |   |
|--------------------|---|
| Part number        | 09 15 100 0307  |
| Specification      | Han M23 HBM back 2,7mm  |
| HARTING eCatalogue | <a href="https://b2b.harting.com/09151000307">https://b2b.harting.com/09151000307</a> |

### Identification

|                             |                             |
|-----------------------------|-----------------------------|
| Category                    | Hoods/Housings              |
| Series of hoods/housings    | Han <sup>®</sup> M23 Signal |
| Type of hood/housing        | Bulkhead mounted housings   |
| Description of hood/housing | Rear mounting               |

### Version

|              |  |
|--------------|--|
| Locking type | Screw locking<br>ComLock rapid locking |
| Size         | M23                                    |
| Fixing       | Fixing hole 4 x 2.7 mm                 |

### Technical characteristics

|  |  |
|--|--|
| Limiting temperature                   | -40 ... +125 °C  |
| Degree of protection acc. to IEC 60529 | IP67 in locked position<br>IP69 / IPX9K acc. to ISO 20653 in locked position |

### Material properties

|                             |  |
|-----------------------------|--|
| Material (hood/housing)     | Copper-zinc alloy                                    |
| Surface (hood/housing)      | Nickel plated  |
| Material (seal)             | NBR  |
| Colour (seal)               | Black  |
| RoHS                        | compliant with exemption                             |
| RoHS exemptions             | 6c: Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                             |
| China RoHS                  | 50   |
| REACH Annex XVII substances | No   |
| REACH ANNEX XIV substances  | No   |
| REACH SVHC substances       | Yes  |



Pushing Performance

## Material properties

|                       |      |
|-----------------------|------|
| REACH SVHC substances | Lead |
|-----------------------|------|

## Specifications and approvals

|          |                       |
|----------|-----------------------|
| UL / CSA | UL 1977 ECBT2.E235076 |
|----------|-----------------------|

## Commercial data

|                                |  |
|--------------------------------|--|
| Packaging size                 | 5  |
| Net weight                     | 25.5 g                                   |
| Country of origin              | Germany                                  |
| European customs tariff number | 85389099                                 |
| eCl@ss                         | 27440202 Shell for industrial connectors |