

Han M23 Hood cable to cable 3-7 mm



Part number	09 15 100 0701
Specification	Han M23 Hood cable to cable 3-7 mm
HARTING eCatalogue	https://b2b.harting.com/09151000701

Identification

Category	Hoods/Housings
Series of hoods/housings	Han [®] M23 Signal
Type of hood/housing	Cable to cable housing
Description of hood/housing	EMC version

Version

Locking type	Screw locking ComLock rapid locking
Size	M23
Version	Top entry

Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 in locked position IP69 / IPX9K acc. to ISO 20653 in locked position
Clamping range	3 ... 7 mm

Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
Material (seal)	NBR
Colour (seal)	Black
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes



Pushing Performance

Material properties

REACH SVHC substances	Lead
-----------------------	------

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

Commercial data

Packaging size	5
Net weight	74.4 g
Country of origin	Germany
European customs tariff number	85389099
