

## Han M23 17 Female -soldered contact



Part number	09 15 117 2703
Specification	Han M23 17 Female -soldered contact
HARTING eCatalogue	<a href="https://b2b.harting.com/09151172703">https://b2b.harting.com/09151172703</a>

### Identification

Category	Inserts
Series	Han <sup>®</sup> M23 Signal
Element	Inserts

### Version

Termination method	PCB solder termination
Gender	Female
Number of contacts	17
Details	Suitable for bulkhead mounted housings 09 15 100 0301, 0302, 0305, 0306 and 0307 only!

### Technical characteristics

Rated current	8 A
Rated voltage	160 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	> 10 <sup>6</sup> Ω
Limiting temperature	-40 ... +125 °C
Mating cycles	≥500

### Material properties

Material (insert)	Polyamide
Colour (insert)	White
Material (contacts)	Copper alloy



Pushing Performance

## Material properties

Surface (contacts)	Gold plated
Material flammability class acc. to UL 94	V-0
RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	27.4 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440205 Contact insert for industrial connectors