




Pushing Performance

## Circular Connector with Harax M 1 2/ 4-p



Part number	21 03 112 2405
Specification	Circular Connector with Harax M 1 2/ 4-p
HARTING eCatalogue	<a href="https://b2b.harting.com/21031122405">https://b2b.harting.com/21031122405</a>

### Identification

Category	Connector
Series	Circular connectors M12
Element	Cable connector
Specification	Straight

### Version

Termination method	HARAX <sup>®</sup> connection technology
Gender	Female
Locking type	Screw locking
Shielding	Unshielded
Number of contacts	4
Coding	A-coding

### Technical characteristics

Conductor cross-section	0.25 ... 0.5 mm <sup>2</sup>
Conductor cross-section	AWG 24 ... AWG 20
Wire outer diameter	≤1.6 mm
Rated current	4 A
Rated voltage	32 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	> 10 <sup>8</sup> Ω
Contact resistance	≤10 mΩ
Ambient temperature	-40 ... +85 °C



Pushing Performance

## Technical characteristics

Tightening torque	0.6 Nm
Wrench size	A/F 13 Knurled screw / knurled nut
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP65 when mated IP67 when mated
Cable diameter	4 ... 5.1 mm
Overvoltage category	III
Isolation group	I (600 ≤ CTI)

## Material properties

Material (insert)	Polyamide
Material (contacts)	Brass
Surface (contacts)	Gold plated
Material (hood/housing)	Polyamide Zinc die-cast
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	No

## Specifications and approvals

Specifications	IEC 61076-2-101
UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079

## Commercial data

Packaging size	1
Net weight	24 g
Country of origin	Germany
European customs tariff number	85366990
eCl@ss	27440102 Circular connector (for field assembly)