

## USB-C Multiport Video Adapter - 4-in-1 - 95W Power Delivery - Space Gray

Product ID: CDPVDHMDPDP



This USB-C multiport video adapter offers a portable solution for connecting your USB Type-C laptop to a VGA, DVI, HDMI or Mini DisplayPort (mDP) display. It features USB Power Delivery, so you can power your laptop while outputting video using the same USB-C port.

### Power and Video in One Port

This USB-C adapter supports USB Power Delivery up to 95 watts and features an additional USB-C port. You can charge your laptop using its USB-C power adapter, even while you output video. Many laptops support charging through a USB-C port with Power Delivery, check your specifications to confirm compatibility.

## **All-in-One Video Connectivity with Travel in Mind**

Carry one adapter instead of four. This versatile 4-in-1 monitor adapter lets you connect your USB-C laptop to any display. With its durable aluminum enclosure and a magnetic retainer that secures the breakout cable in place while you're not using it, the adapter is rugged enough to carry in your travel bag.

## **Astonishing Picture Quality**

The HDMI and mDP outputs support UHD 4K resolutions, providing four times the picture quality of high-definition 1080p. All of the outputs (HDMI, mDP, VGA, DVI) support high-definition resolutions up to 1920 x 1200. The adapter is compatible with USB-C DP Alt Mode devices.

## **Stylish Connectivity**

The USB-C adapter has a Space Gray trim and built-in USB-C cable designed to match your Space Gray MacBook, or MacBook Pro.

CDPVDHMDPDP is backed by a StarTech.com 3-year warranty and free lifetime technical support.

### Certifications, Reports and Compatibility



### Applications

- Connect to virtually any display while traveling
- Connect a MacBook or USB-C laptop to a VGA, DVI, HDMI or mDP display
- Connect a secondary monitor to your Space Gray MacBook or USB-C laptop

### Features

- Charge your laptop while connecting a display using just one USB-C port, with USB Power Delivery
- Maximize your video compatibility with a 4-in-1 adapter: USB-C to VGA, DVI, HDMI or Mini DisplayPort
- Space Gray trim matches your Space Gray MacBook or MacBook Pro
- Supports resource-demanding applications with UHD resolutions up to 4K 60Hz
- Maximum portability with a built-in magnetic cable manager

<b>Hardware</b>	Warranty	3 Years
	Active or Passive Adapter	Active
	Adapter Style	Adapters
	AV Input	USB Type-C
	AV Output	DVI HDMI VGA Mini-DisplayPort
	Chipset ID	Parade - PS176 VIA/VLI - VL102 ITE -IT6516
<b>Performance</b>	Audio Specifications	<b>HDMI or mDP output:</b> 7.1 surround sound
	Maximum Analog Resolutions	1920 x 1200 @ 60Hz
	Maximum Digital Resolutions	4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz (HDMI) 4096 X 2160 @ 60Hz (mDP)
	Supported Resolutions	<b>Maximum HDMI output:</b> 4096 X 2160 @ 24Hz or 3840 X 2160 @ 60Hz <b>Maximum mDP output:</b> 4096 X 2160 @ 60Hz <b>Maximum DVI and VGA output:</b> 1920 x 1200 @ 60Hz <i>Lower resolutions and refresh rates may also be supported</i>
	Video Revision	HDMI 2.0 DisplayPort 1.2
	Wide Screen Supported	Yes
<b>Connector(s)</b>	Connector A	1 - USB-C (24 pin) DisplayPort Alt Mode Male Input
	Connector B	1 - Mini-DisplayPort (20 pin) Female Output 1 - VGA (15 pin, High Density D-Sub) Female Output 1 - DVI-I (29 pin) Female Output 1 - HDMI (19 pin) Female Output 1 - USB-C (24 pin) USB Power Delivery only Female Input
<b>Special Notes / Requirements</b>	<b>Note</b>	Only one video output is supported on the video adapter at a time, if multiple connections are made, only one of the outputs will function

Your laptop may have specific requirements for charging. This USB-C multiport adapter supports USB Power Delivery 3.0, up to 95W. When using your laptop's USB-C power adapter, the multiport adapter powers both the adapter and your laptop - with up to 85W charging available for laptop charging. For more information on your laptop's charging requirements, refer to the manufacturer of your laptop.

<b>Power</b>	Laptop Charging via Power Delivery	85W
	Power Consumption (In Watts)	10W
	Power Delivery	95W
	Power Source	USB-Powered
<b>Environmental</b>	Humidity	0~95% RH
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	0°C to 60°C (32°F to 140°F)
<b>Physical Characteristics</b>	Accent Color	Black & Space Gray
	Cable Length	101 mm [4 in]
	Color	Black
	Enclosure Type	Aluminum
	Product Height	1.8 cm [0.7 in]
	Product Length	10.9 cm [4.3 in]
	Product Width	57 mm [2.2 in]
	Weight of Product	128 g [4.5 oz]
<b>Packaging Information</b>	Package Height	30 mm [1.2 in]
	Package Length	17.5 cm [6.9 in]
	Package Width	14.2 cm [5.6 in]
	Shipping (Package) Weight	0.2 kg [0.5 lb]
<b>What's in the Box</b>	Included in Package	1 - Travel A/V Adapter

Product appearance and specifications are subject to change without notice.