

Full screen 6.1" smartphone featuring triple-lens camera, octa core processor and 3+32GB memory in a gradient body

## VARIETY OF COLORS



dark night



cosmic ultraviolet



HD+ IPS Display



32GB Internal Storage



13.0 Mpx Triple-lens Camera



Touch ID



LTE



3000mAh battery



- Full screen with waterdrop notch: see more and hold less with 6.1" huge IPS display with 19.5:9 aspect ratio. Enjoy the comfort of bezel-less phone with HD+ resolution
- Octa core processor: ensures more advanced tasks such as handling high resolution videos and graphic-heavy games without draining the battery
- Beautiful design: body with gradient back and 2.5D curved screen glass, available in 2 color options: dark night and cosmic ultraviolet
- Advanced photo and video: advanced 13.0MP AF triple-lens camera with flash for excellent clear & vivid shots. A range of shooting modes, filters and Emoji will boost your creativity
- Selfie expert: 5.0MP camera with a range of features for high quality photos
- Capacious: 32GB of internal storage on board and possibility to expand it with microSDHC cards up to 128GB
- 360 OS user interface based on Android 8.1 Oreo: better user experience, improved battery management, built-in theme store for customization and lots of other features
- Powerful battery: 3000 mAh battery for long performance without charging
- Fingerprint scanner: protects your data in a more reliable and intelligent way. While Face recognition ensures easy unlock
- 4G LTE Internet connection: streaming without interruption, seamlessly playing multi-player games and browsing faster than ever before
- Dual SIM: for optimizing budget on calls and Internet
- Back case: free accessory in the box for additional protection from scratches and damage
- High quality package: stylish and minimal design, thick carton

<b>SIM card slot</b>	Dual SIM: LTE + WCDMA
<b>Display</b>	Size: 6.1" Resolution: HD+ (1560 x 720), 19.5:9 Technology: IPS, in-cell, 2.5D curved glass
<b>Processor</b>	SharkL3 4x1.6GHz + 4x1.2GHz octa core
<b>Memory</b>	Built-in: 3 GB RAM + 32 GB eMMC Expandable: slot for microSDHC card up to 128GB
<b>Power</b>	3000 mAh Li-po battery
<b>OS</b>	360 OS based on Android 8.1 Oreo
<b>Imaging</b>	Front: 5.0MP Rear: 13.0MP AF triple-lens camera with flash light

<b>Network</b>	4G LTE: 800/1800/2100/2600 MHz 3G WCDMA: 900/2100MHz 2G GSM: 850/900/1800/1900MHz
<b>Connectivity</b>	BT 4.0+HS, Wi-Fi: 802.11b g n USB: microUSB 2.0
<b>Audio</b>	Mic, speakers, 3.5 jack
<b>Built-in devices</b>	Fingerprint scanner, GPS, FM
<b>Dimensions</b>	157 x 74 x 9.5 mm
<b>Weight</b>	180g (with battery)
<b>In the box</b>	Back case, USB cable, AC charger, screen protective film