



ES5542.CR.BG

High precision Ergo-tek Slim Cutters - Small Tapered & Relieved head, full-flush. OAL: 120 mm. ESD safe



Pointed head shape and deep relief for a very low profile to maximize accessibility when limited space.

High precision Cutters & Pliers leaflet

Documents

Grip handle material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High Precision Cutters
Kit	no
ESD safe	yes
Body material	100Cr6
Grip handle material	Ergo-tek Slim - TPE + PP
Head shape	

	Tapered & Relieved
Head width (mm - in) - C	10.00 - 0.394
Size/type	Small
Cutting edges	Full-Flush
OAL (mm - in) - A	120.00 - 4.724
B (mm - in)	10.00 - 0.394
Head thickness (mm - in) - D	6.40 - 0.252
F (mm - in)	0.50 - 0.02
Cutting capacity soft (mm)	0.1-0.8
Cutting capacity soft (AWG)	38-20
Cutting capacity medium (mm)	0.1-0.4
Cutting capacity medium (AWG)	38-26
Net weight (g-lb)	81 - 0.179
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com