



## ES6022.CR.BG

High precision Ergo-tek Slim Pliers - Snipe Nose, Serrated Jaws. OAL: 130 mm. ESD safe



Commonly used in electronic assembly and rework, as well as in fine jewellery.

***High precision Cutters & Pliers leaflet***

## Documents

 Grip handle material TDS

## Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	High Precision Pliers
Kit	no
ESD safe	yes
Body material	100Cr6
Grip handle material	Ergo-tek Slim - TPE + PP
Head shape	Snipe Nose

<b>Head width (mm - in) - C</b>	10.00 - 0.394
<b>Size/type</b>	Short
<b>Jaw (smooth/serrated)</b>	Serrated
<b>OAL (mm - in) - A</b>	130.00 - 5.118
<b>B (mm - in)</b>	20.00 - 0.787
<b>Head thickness (mm - in) - D</b>	6.40 - 0.252
<b>E (mm - in)</b>	1.00 - 0.039
<b>F (mm - in)</b>	0.50 - 0.02
<b>Net weight (g-lb)</b>	84 - 0.185
<b>RoHS compliant</b>	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com