




ES352TX.CR.BG

High precision Ergo-tek Slim Tungsten carbide Cutters - Large Tapered head, Tungsten carbide tips, full-flush. OAL: 118 mm. ESD safe



- Engineered for hard wires
- Tungsten carbide blades
- 81 HRC hardness

Tungsten Carbide sharp tip - Large Tapered diagonal cutters

Tungsten carbide cutter leaflet

Documents

Grip handle material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Tungsten Carbide Cutters
Kit	no
ESD safe	yes

Body material	100Cr6
Tip material	TX
Grip handle material	Ergo-tek Slim - TPE + PP
Head shape	Tapered
Head width (mm - in) - C	12.50 - 0.492
Size/type	Large
Cutting edges	Full-Flush
OAL (mm - in) - A	118.00 - 4.646
B (mm - in)	7.50 - 0.295
Head thickness (mm - in) - D	6.40 - 0.252
E (mm - in)	0.70 - 0.028
F (mm - in)	0.40 - 0.016
Net weight (g-lb)	83 - 0.183
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland
T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com