



ES141TX.CR.BG

High precision Ergo-tek Slim Tungsten carbide Cutters - Small Oval head, Tungsten carbide tips, flush. OAL: 120 mm. ESD safe



- Engineered for hard wires
- Tungsten carbide blades
- 81 HRC hardness

Tungsten Carbide sharp tip - Small Oval diagonal cutters

Tungsten carbide cutter leaflet

Documents

 Grip handle material TDS

Product Details

Market - MEDICAL DEVICE	yes
Market - LIFE SCIENCE & MICROSCOPY	yes
Market - ELECTRONICS	yes
Market - WATCHMAKING & JEWELRY	yes
Category	Tungsten Carbide Cutters
Kit	no
ESD safe	yes

Body material	100Cr6
Tip material	TX
Grip handle material	Ergo-tek Slim - TPE + PP
Head shape	Oval
Head width (mm - in) - C	10.00 - 0.394
Size/type	Small
Cutting edges	Flush
OAL (mm - in) - A	120.00 - 4.724
B (mm - in)	10.00 - 0.394
Head thickness (mm - in) - D	6.40 - 0.252
Net weight (g-lb)	83 - 0.183
RoHS compliant	yes



© 2019 IDEAL-TEK SA

via Giuseppe Motta 4, 6828 Balerna - Switzerland

T +41 91 683 32 29 - F +41 91 683 03 71 - E info@ideal-tek.com